

# Product data sheet

Specifications



NEMA Motor Starter, Type S,  
replacement coil, 110/120VAC  
50/60Hz, 2 or 3 pole, NEMA Size 2  
starter and 8903SP lighting

3106340938

Product availability: Stock - Normally stocked in distribution facility

Price\*: 140.00 USD

## Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

## Complementary

Nema Size	2
[Ue] Rated Operational Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Inrush Power In Va	296 VA 311 VA
Average Consumption	36 VA 37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

## Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
Gtin	785901484882
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	12.80 oz (362.874 g)

## Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope