

# Product data sheet

Specifications



## NEMA Motor Starter, Type S, replacement coil, 24VAC 60Hz, 2 or 3 pole, NEMA size 3 starter and 8903SQ lighting

3107440016

! Discontinued

! Discontinued on: Dec 18, 2023

Product availability: Stock - Normally stocked in distribution facility

### Main

|                                       |   |
|---------------------------------------|---|
| Product Or Component Type             | Coil  |
| Accessory / Separate Part Destination | Class 8502 type SE contactor<br>Class 8903 type SQ lighting contactor<br>Class 8910 type DPA12/SYD138 contactor |

### Complementary

|                                |                    |
|--------------------------------|--------------------|
| Nema Size                      | 3                  |
| [Ue] Rated Operational Voltage | 24 V AC 60 Hz      |
| Inrush Power In Va             | 700 VA             |
| Average Consumption            | 46 VA              |
| Height                         | 2.87 in (73 mm)    |
| Width                          | 2.56 in (65 mm)    |
| Depth                          | 0.08 in (2.093 mm) |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1CP1018079 |
| Discount Schedule | CP10         |
| Gtin              | 785901110507 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

### Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type Of Package 1       | PCE                  |
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 2.20 in (5.588 cm)   |
| Package 1 Width              | 2.80 in (7.112 cm)   |
| Package 1 Length             | 3.30 in (8.382 cm)   |
| Package 1 Weight             | 13.60 oz (385.554 g) |

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months