Product data sheet

Specification





MN delay unit, MasterPact NT/ NW, ComPacT NS, adjustable time delay 0.5s to 3s, 48/60VDC, 48/60VAC 50/60Hz, spare part

33680

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 117.00 USD

Main

Device Short Name	MN delay unit	
Product Or Component Type	Time delay relay	
Device Application	Control	
Range Compatibility	Masterpact MasterPact NT	
	Masterpact MasterPact NW	
	ComPact ComPact NSX	
	ComPact ComPact NS630b1600	
	ComPact ComPact NS1600b3200	
	PowerPact PowerPact Multistandard	
	ComPact ComPact NSXm	
	ComPact ComPact NSX DC	
	Masterpact MasterPact NW UL 489	
	Masterpact MasterPact NT UL 489	
	Masterpact MasterPact NW DC	
Voltage Release Type	Undervoltage release	
[Uc] Control Circuit Voltage	Control Circuit Voltage 4860 V AC 50/60 Hz 4860 V DC	

Complementary

Impulse Duration	200 ms	
Time Delay Range	0.53 s	
Threshold Tripping Voltage	0.350.7 Un open 0.85 Un close	
Supply Holding Power	4.5 VA	
Supply Inrush Power	200 VA	
Mounting Mode	External mounting	
Response Time	0.5 s 1 s 1.5 s 3 s	
Accessory / Separate Part Category	Spare part Compact NS630b1600 Spare part Compact NS1600b3200	

Ordering and shipping details

Category	US1DE2F01291		
Discount Schedule	DE2F		
Gtin	3303430336808		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	FR	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.31 in (8.4 cm)
Package 1 Width	2.99 in (7.6 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	7.55 oz (214.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.57 lb(US) (4.339 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	