



Main

Product or component type	Dry Sealed Transformer
Primary Voltage	600 V
Secondary Voltage	120/240 V
Full Capacity Taps	2 5 % FCBN

Complementary

Enclosure Code	10A
Phase	1 phase
Primary to Secondary Voltage	600 V : 120/240 V
Power Rating	3 kVA
Temperature rise	115 °C
Height	10.5 in
Width	8.62 in
Depth	6.5 in
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA cULus UL listed

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations