

Product data sheet

Specifications

SQUARE D

Green Premium™



Transformer, dry type,
encapsulated, 3kVA, 1 phase,
277V primary, 120/240V
secondary, 10A, 115C rise

3S8F

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 2,556.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	277 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	10A
Phase	1 phase
Power Rating	3 kVA
Temperature Rise	115 °C
Height	10.5 in (266.70 mm)
Width	8.62 in (218.95 mm)
Depth	6.5 in (165.10 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	CSA cULus UL Listed

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901015543
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	11.50 in (29.21 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	16.75 in (42.545 cm)
Package 1 Weight	55.20 lb(US) (25.038 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov