

Product data sheet

Specifications

SQUARE D



TRANSFORMER DRY 3PH 40KVA 575V-460Y/265V

40T147HDIT

Discontinued on: Jan 2, 2024

Discontinued

Main

Product	Drive Isolation Transformer
Enclosure Code	18D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
Phase	3 phase
Primary Voltage	575 V delta
Power Rating	40 kVA
Secondary Voltage	460Y/265 V
Full Capacity Taps	2 5 % 1+ 1-
Temperature Rise	150 °C
Winding Material	Aluminium

Ordering and shipping details

Category	16266-DRIVE ISOLATION TRANSFORMERS
Discount Schedule	PE2
Gtin	3606486988275
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	395.00 lb(US) (179.169 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
