Product data sheet

Specification





ground fault protector GFP - 4 poles - 63A - 240..480V - 100mA SIE

60996

! Discontinued on: Jul 12, 2021

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Multi9
Product Name	Multi9 GFP
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	GFP
Poles Description	4P
Neutral Position	Left
Line Rated Current	63 A
Network Type	AC
Earth-Leakage Sensitivity	100 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC-SIE
Rated Conditional Short-Circuit Current	10 kA
Utilisation Category	AC-23A

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC 60 Hz
	480Y/277 V AC 60 Hz
	230/400 V AC 50 Hz
	240/415 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Control Type	Toggle
Local Signalling	Fault indication
Connection Pitch	0.71 in (18 mm) between phases
9 Mm Pitches	8
Height	3.19 in (81 mm)
Width	2.83 in (72 mm)
Depth	2.95 in (75 mm)
Net Weight	15.87 oz (450 g)
Color	Gray

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical Durability	20000 cycles	
Provision For Padlocking	Padlockable	
Locking Options Description	Padlocking in OFF position	
Connections - Terminals	Tunnel type terminals 0.000.05 in² (2.535 mm²) flexible Tunnel type terminals 0.000.05 in² (2.535 mm²) rigid	
Tightening Torque	30.98 lbf.in (3.5 N.m)	

Environment

Standards	UL 1053 IEC 61008
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 conforming to IEC 60529 IPxx B conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-13140 °F (-2560 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
Gtin	785901666721
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.99 in (7.6 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	3.62 in (9.2 cm)
Package 1 Weight	13.62 oz (386 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.