

# Product data sheet

## Characteristics

# 7B2

## 9007MS/ML limit switch lever - zinc - fixed length - outside steel roller

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 13.60 USD



### Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 22.35 mm (0.88 in) -
Type of roller	1 steel outside roller 19.05 mm (0.75 in) 12.70 mm (0.5 in)
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Net weight	0.05 kg (0.1 lb(US))

### Environment

Ambient air temperature for operation	-40...105 °C (-40...221 °F)
Ambient air temperature for storage	-40...105 °C (-40...221 °F)
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1

GTIN	00785901121657
Package weight(Lbs)	0.05 kg (0.1 lb(US))
Returnability	No
Country of origin	MX

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

### Contractual warranty

Warranty	18 months
----------	-----------