



Price\*\* : 13.60 USD



7B7N has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 1.75 in -
Type of roller	1 nylon outside roller diameter: 0.75 in - width: 0.5 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-40...221 °F
Ambient air temperature for storage	-40...221 °F
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001

---

Returnability	N
Country of origin	MX

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---