

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 22.70 USD



### Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 2 in -
Type of roller	1 nylon outside roller diameter: 0.75 in - width: 0.75 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-40...221 °F
Ambient air temperature for storage	-40...221 °F
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	00785901216278
Nbr. of units in pkg.	1

Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------