





Transformer, dry type, encapsulated, 7kVA, 1 phase, 240x480V primary, 120/240V secondary, 13B, 115C rise

7S1F

Product availability: Stock - Normally stocked in distribution facility

Price\*: 2,954.00 USD

## Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	240 x 480 V 120/240 V

# Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	7.5 kVA
Temperature Rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

## **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed cULus CSA

# Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901359555
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	13.78 in (35.000 cm)
Package 1 Width	9.45 in (24.000 cm)
Package 1 Length	15.35 in (39.000 cm)
Package 1 Weight	151.57 lb(US) (68.750 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	6
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	935.86 lb(US) (424.500 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov