

Product data sheet

Characteristics

7S7F

TRANSFORMER DRY 1PH 7.5KVA

208V-120/240V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 3,216.00 USD



Main

Product or component type	Dry Sealed Transformer
Primary Voltage	208 V
Secondary Voltage	120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	13B
Phase	1 phase
Primary to Secondary Voltage	208 V : 120/240 V
Power Rating	7.5 kVA
Temperature rise	115 °C
Height	14.75 in
Width	9.75 in
Depth	11.75 in
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA cULus UL listed

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
----------	-------------------------

Discount Schedule	PE2
GTIN	00785901338444
Nbr. of units in pkg.	1
Package weight(Lbs)	135
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------