





Transformer, dry type, encapsulated, 7.5kVA, 1 phase, 208V primary, 120/240V secondary, 13B, 115C rise

7S7F

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 4,342.00 USD

#### Main

| Product Or Component Type    | Dry Sealed Transformer |
|------------------------------|------------------------|
| Primary To Secondary Voltage | 208 V 120/240 V        |
| Full Capacity Taps           | 0                      |

## Complementary

| Enclosure Code     | 13B                  |
|--------------------|----------------------|
| Phase              | 1 phase              |
| Power Rating       | 7.5 kVA              |
| Temperature Rise   | 115 °C               |
| Height             | 14.75 in (374.65 mm) |
| Width              | 9.75 in (247.65 mm)  |
| Depth              | 11.75 in (298.45 mm) |
| Enclosure Mounting | Wall mounted         |
| Enclosure Material | Painted sheet steel  |

#### **Environment**

| Enclosure Type         | NEMA 3R          |
|------------------------|------------------|
| Insulation Temperature | 356 °F (180 °C)  |
| Product Certifications | CSA<br>UL Listed |

## Ordering and shipping details

| Category          | US10PE216277 |
|-------------------|--------------|
| Discount Schedule | 0PE2         |
| Gtin              | 785901338444 |
| Returnability     | No           |
| Country Of Origin | US           |

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Number Of Units In Package 1 | 1                         |
|------------------------------|---------------------------|
| Package 1 Height             | 14.10 in (35.814 cm)      |
| Package 1 Width              | 14.50 in (36.83 cm)       |
| Package 1 Length             | 10.90 in (27.686 cm)      |
| Package 1 Weight             | 135.00 lb(US) (61.235 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

| <b>⊘</b> | Reach Free Of Svhc             |
|----------|--------------------------------|
| <b>⊘</b> | Toxic Heavy Metal Free         |
| <b>⊘</b> | Mercury Free                   |
| <b>⊘</b> | Rohs Exemption Information Yes |
| <b>⊘</b> | Pvc Free                       |

#### **Certifications & Standards**

| Reach Regulation                | REACh Declaration   |
|---------------------------------|---|
| Eu Rohs Directive               | Compliant   |
|                                 | EU RoHS Declaration   |
| China Rohs Regulation           | China RoHS declaration  |
|                                 | Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| <b>Environmental Disclosure</b> | Product Environmental Profile   |
| Circularity Profile             | No need of specific recycling operations  |
| California Proposition 65       | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
|                                 |   |