

Product data sheet

Characteristics

7XA2

9007MS/ML limit switch lever - zinc - fixed length - inside steel roller

Price** : 19.60 USD



7XA2 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 22.35 mm (0.88 in) -
Type of roller	1 steel inside roller 19.05 mm (0.75 in) 6.35 mm (0.25 in)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	0.875 in
Switch actuation	By 30° cam
Net weight	0.05 kg (0.1 lb(US))

Environment

Ambient air temperature for operation	-40...105 °C (-40...221 °F)
Ambient air temperature for storage	-40...105 °C (-40...221 °F)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22449-LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
Package weight(Lbs)	1.60 oz (45.359 g)
Returnability	No
Country of origin	MX

Contractual warranty

Warranty	18 months
----------	-----------
