

# Product data sheet

## Characteristics

# 8501CDO15V64

Power Relay, SPDT, 1NO and 1NC, 1.5 HP, 30 A resistive at 300 VAC, 220 VDC coil

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 69.54 USD



### Main

Product range	Power Relay 8501C
Product type	Power relay
Short name	Type C
[In] rated line current	30 A
Device application	Suited for controlling small single phase motors and other light loads
Switch function	SPDT
Contact composition	1 NO/1 NC
[Uc] control circuit voltage	220 V DC
Horsepower rating	1.5 hp
Maximum switching voltage	600 V AC

### Complementary

Class number	8501
Phase	1 phase
Terminal connects	Screw clamp terminal
Wire range	AWG 10 copper
Terminal tightening torque	1.24... 1.69 N.m (11... 15 lbf.in)
Coil burden	2 W
Mounting	Panel mounting

### Environment

Ambient temperature range - operational	-30...60 °C (-22...140 °F)
Product certifications	UL listed file E78351 CCN NLDX CSA CE

Height	61.72 mm (2.43 in)
Width	63.50 mm (2.5 in)
Depth	55.37 mm (2.18 in)

### Ordering and shipping details

Category	21131 - 8501 C
Discount Schedule	CP2
Package weight(Lbs)	0.22 kg (0.49 lb(US))
Returnability	No
Country of origin	CN

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds and Di-isodecyl phthalate (DIDP) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------