

Product data sheet

Specifications

SQUARE D

Green Premium™



Power Relay, Type C, DPDT, 2 normally open and 2 normally closed contacts, 20A resistive at 110 VDC, 120 VAC coil

8501CO22V20

Product availability: Stock - Normally stocked in distribution facility

Price*: 102.48 USD

Main

Product Range	Power Relay 8501C
Product Type	Power relay
Short Name	type C
[In] Rated Line Current	20 A
Device Application	Suited for controlling small single phase motors and other light loads
Switch Function	DPDT
Contact Composition	2 NO/2 NC
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz
Maximum Switching Voltage	325 V DC

Complementary

Class Number	8501
Phase	1 phase
Terminal Connects	Screw clamp terminal
Wire Range	AWG 10 copper
Terminal Tightening Torque	11...15 lbf.in (1.24...1.69 N.m)
Coil Burden	10 VA
Mounting	Panel mounting

Environment

Ambient Temperature Range - Operational	-22...122 °F (-30...50 °C)
Product Certifications	UL listed file E78351 CCN NLDX CSA CE
Height	3.12 in (79.25 mm)
Width	2.5 in (63.50 mm)
Depth	2.53 in (64.26 mm)

Ordering and shipping details

Category	US10CP221131
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0CP2
Gtin	785901052241
Returnability	Yes
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	11.20 oz (317.515 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov