



Price\*\* : 22.70 USD



⚠ Discontinued

### Main

Product range	8501K
Product type	Relay
Relay type	General purpose
Mounting type	Socket
Contact composition	DPDT
[Uc] control circuit voltage	24 V AC
Pilot light	No indicator
Manual operator	Without test button

### Complementary

Horsepower rating	0.33 hp at 120 V 0.5 hp at 240 V
Breaking capacity	3 A at 120 V AC - inductive control circuit per UL 508 1.5 A at 240 V AC - inductive control circuit per UL 508 15 A at 120 V AC - resistive control circuit per UL 508 10 A at 240 V AC - resistive control circuit per UL 508 10 A at 28 V DC - resistive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Silver tin oxide
Operating time	8 ms - pick-up 8 ms - drop-out
Shape of pins	Spade
For use with	8501NR82

### Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	UL recognized UL listed

	CE CSA RoHS
Height	2.07 in
Width	1.52 in
Depth	1.42 in

### Ordering and shipping details

Category	21144 - 8501 KU
Discount Schedule	CP2
GTIN	00785901480860
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Returnability	N
Country of origin	CN

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0702 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

### 8501KU12V14 is replaced by:



#### 8510K General Purpose Plug-In Relays 8501KUR12V14

Plug in relay, 8 blade, DPDT, 10 amp at 277 VAC, 24 VAC coil

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017