

# Product data sheet

Specifications



## Plug-In Relay - 8 blade plug-in - 2 poles - 6VAC coil

8501KU12V35

Discontinued on: Oct 11, 2019

Discontinued

### Main

Product Range	8501K
Product Type	Relay
Relay Type	General purpose
Mounting Type	Socket
Contact Composition	DPDT
[Uc] Control Circuit Voltage	6 V AC
Pilot Light	No indicator
Manual Operator	Without test button

### Complementary

Horsepower Rating	0.33 hp 120 V AC 0.5 hp 240 V AC
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 10 A 240 V AC resistive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Silver tin oxide
Operating Time	8 ms - pick-up 8 ms - drop-out
Shape Of Pins	Spade
For Use With	8501NR82

### Environment

Ambient Temperature Range - Operational	-40...131 °F (-40...55 °C)
Product Certifications	UL Listed CSA UL Recognized CE
Height	2.07 in (52.58 mm)
Width	1.52 in (38.61 mm)
Depth	1.42 in (36.07 mm)

### Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	21144-8501 KU
Discount Schedule	CP2
Gtin	00785901059202
Returnability	No
Country Of Origin	CN

## Contractual warranty

Warranty	18 months
----------	-----------