





Plug-In Relay - 11 blade plug-in - 3 poles - 24VAC coil

8501KU13V14

Discontinued on: Oct 11, 2019

① Discontinued

Main

Product Range	8501K
Product Type	Relay
Relay Type	General purpose
Mounting Type	Socket
Contact Composition	3PDT
[Uc] Control Circuit Voltage	24 V AC
Pilot Light	No indicator
Manual Operator	Without test button

Complementary

Horsepower Rating	0.33 hp 120 V AC 0.5 hp 240 V AC
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508 10 A 120 V AC resistive control circuit UL 508 6.66 A 240 V AC resistive control circuit UL 508
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Silver tin oxide
Operating Time	8 ms - pick-up 8 ms - drop-out
Shape Of Pins	Spade
For Use With	8501NR82

Environment

Ambient Temperature Range - Operational	-40113 °F (-4045 °C)
Product Certifications	CE CSA UL Listed UL Recognized
Height	2.07 in (52.58 mm)
Width	1.52 in (38.61 mm)
Depth	1.42 in (36.07 mm)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	21144-8501 KU
Discount Schedule	CP2
Gtin	00785901480815
Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov