Product data sheet

Specifications



Relay, miniature plug in, 10 A, 3 poles, 24 VAC coil, pilot light, test

8501RS43M1P14V14

() Discontinued on: Oct 11, 2019



Main

Product Range	8501R	
Product Type	Miniature Relay	
Relay Type	Standard	

Complementary

Mounting Type	Socket	
Contact Composition	3PDT	
[Uc] Control Circuit Voltage	24 V AC	
Pilot Light	Green indicator relay energised LED	
Manual Operator	Test button	
Horsepower Rating	0.5 120 V AC 1 277 V AC	
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 120 V AC resistive control circuit UL 508 6.67 A 277 V AC resistive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508	
Maximum Switching Voltage	300 V AC 30 V DC	
Contact Material	Silver alloy, gold flashed	
Operating Time	20 ms - pick-up 20 ms - drop-out	
Shape Of Pins	Spade	
For Use With	8501NR43	
Height	1.07 in (27.3 mm)	
Width	1.20 in (30.6 mm)	
Depth	1.65 in (41.8 mm)	

Environment

Ambient Temperature Range - Operational	-40131 °F (-4055 °C)
Product Certifications	UL Listed UL Recognized
	CSA CE

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	21143-8501 R	
Discount Schedule	CP2	
Gtin	00785901695714	
Returnability	No	
Country Of Origin	CN	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov