Product data sheet

Specifications

SQUARE D





Plug in relay, Type R, miniature, 0.167 HP at 120 VAC, 3A resistive at 277 VAC, 14 blade, 4PDT, 4 NO, 4 NC, 24 VDC coil

8501RSD24V53

Product availability: Stock - Normally stocked in distribution facility

Price*: 64.66 USD

Main

| Product Range | 8501R |
|---------------|-----------------|
| Product Type | Miniature Relay |
| Relay Type | Low voltage |

Complementary

| Complementary | |
|------------------------------|---|
| Mounting Type | Socket |
| Contact Composition | 4PDT |
| [Uc] Control Circuit Voltage | 24 V DC |
| Pilot Light | No indicator |
| Manual Operator | Without test button |
| Horsepower Rating | 0.167 120 V AC |
| Breaking Capacity | 0.5 A 120 V AC inductive control circuit UL 508 3 A 120 V AC resistive control circuit UL 508 3 A 277 V AC resistive control circuit UL 508 3 A 30 V DC resistive control circuit UL 508 |
| Maximum Switching Voltage | 300 V AC 30 V DC |
| Contact Material | Gold plated bifurcated silver |
| Operating Time | 20 ms - pick-up 20 ms - drop-out |
| Shape Of Pins | Spade |
| For Use With | 8501NR45 |
| Height | 1.10 in (27.9 mm) |
| Width | 0.83 in (21 mm) |
| Depth | 1.63 in (41.5 mm) |

Environment

| Ambient Temperature Range - Operational | -40131 °F (-4055 °C) |
|--|---|
| Product Certifications | UL Listed UL Recognized CSA CE |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

| Category | US10CP221143 |
|-------------------|--------------|
| Discount Schedule | 0CP2 |
| Gtin | 785901031864 |
| Returnability | Yes |
| Country Of Origin | CN |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.30 in (3.302 cm) |
| Package 1 Width | 1.40 in (3.556 cm) |
| Package 1 Length | 2.00 in (5.08 cm) |
| Package 1 Weight | 1.28 oz (36.287 g) |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |