

# 8501RSD41M1P14V53

Relay - miniature plug-in - 12A - 1 pole - 24VDC  
coil - pilot light - test



Price\* : 39.30 USD

8501RSD41M1P14V53 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

## Main

Product range	8501R
Product type	Miniature Relay
Relay type	Standard

## Complementary

Mounting type	Socket
Contact composition	SPDT
[Uc] control circuit voltage	24 V DC
Pilot light	LED green indicator when relay energised
Manual operator	Test button
Horsepower rating	0.5 at 120 V AC 1 at 277 V AC
Breaking capacity	3 A at 120 V AC - inductive control circuit per UL 508 1.5 A at 240 V AC - inductive control circuit per UL 508 15 A at 120 V AC - resistive control circuit per UL 508 10 A at 277 V AC - resistive control circuit per UL 508 15 A at 28 V DC - resistive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Silver alloy, gold flashed
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR41
Height	27.3 mm
Width	0.55 in (14 mm)
Depth	41.8 mm

## Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	CE CSA UL listed UL recognized

## Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
GTIN	00785901218494
Nbr. of units in pkg.	1
Package weight(Lbs)	5.999999999999998E-2
Returnability	N
Country of origin	CN

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------