



Price* : 30.80 USD



⚠ Discontinued

Main

Product range	8501R
Product type	Miniature Relay
Relay type	Low voltage

Complementary

Mounting type	Socket
Contact composition	4PDT
[Uc] control circuit voltage	24 V DC
Pilot light	No indicator
Manual operator	Test button
Horsepower rating	0.1 at 120 V AC 0.1 at 240 V AC
Breaking capacity	3 A at 120 V AC - resistive control circuit per UL 508 3 A at 277 V AC - resistive control circuit per UL 508 3 A at 30 V DC - resistive control circuit per UL 508 1.5 A at 120 V AC - inductive control circuit per UL 508 0.75 A at 240 V AC - inductive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Gold flashed fine silver
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR45
Height	27.9 mm
Width	0.83 in (21 mm)
Depth	1.63 in (41.5 mm)

Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	CE CSA UL listed UL recognized

Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
Nbr. of units in pkg.	25
Package weight(Lbs)	8.999999999999997E-2
Returnability	N
Country of origin	CN

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

8501RSD4M1V53 is replaced by:



Electromechanical relay RXM4GB1BD

Miniature Plug-in relay - Zelio RXM 4 C/O 24 V DC 3 A

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017