

# 8501RSD4M1V56

Relay - miniature plug-in - 3A - 4 poles - 48VDC  
coil - test



Price\* : 30.80 USD



⚠ Discontinued

## Main

Product range	8501R
Product type	Miniature Relay
Relay type	Low voltage

## Complementary

Mounting type	Socket
Contact composition	4PDT
[Uc] control circuit voltage	48 V DC
Pilot light	No indicator
Manual operator	Test button
Horsepower rating	0.1 at 120 V AC 0.1 at 240 V AC
Breaking capacity	3 A at 120 V AC - resistive control circuit per UL 508 3 A at 277 V AC - resistive control circuit per UL 508 3 A at 30 V DC - resistive control circuit per UL 508 1.5 A at 120 V AC - inductive control circuit per UL 508 0.75 A at 240 V AC - inductive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Gold flashed fine silver
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR45
Height	27.9 mm
Width	0.83 in (21 mm)
Depth	1.63 in (41.5 mm)

## Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	CE CSA UL listed UL recognized

## Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
Nbr. of units in pkg.	25
Package weight(Lbs)	8.999999999999997E-2
Returnability	N
Country of origin	CN

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant <b>Will be compliant</b>
REACH	Reference not containing SVHC above the threshold <b>Reference not containing SVHC above the threshold</b>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

8501RSD4M1V56 is replaced by:



### Electromechanical relay RXM4GB1ED

Miniature Plug-in relay - Zelio RXM 4 C/O 48 V DC 3 A

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017