

Product data sheet

Specifications

SQUARE D



Relay, miniature plug in, 3 A, 4 pole, 110 VDC coil, test

8501RSD4M1V60

Discontinued on: Oct 11, 2019

Discontinued

Main

Product Range	8501R
Product Type	Miniature Relay
Relay Type	Low voltage

Complementary

Mounting Type	Socket
Contact Composition	4PDT
[Uc] Control Circuit Voltage	110 V DC
Pilot Light	No indicator
Manual Operator	Test button
Horsepower Rating	0.1 120 V AC 0.1 240 V AC
Breaking Capacity	3 A 120 V AC resistive control circuit UL 508 3 A 277 V AC resistive control circuit UL 508 3 A 30 V DC resistive control circuit UL 508 1.5 A 120 V AC inductive control circuit UL 508 0.75 A 240 V AC inductive control circuit UL 508
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Gold flashed fine silver
Operating Time	20 ms - pick-up 20 ms - drop-out
Shape Of Pins	Spade
For Use With	8501NR45
Height	1.10 in (27.9 mm)
Width	0.83 in (21 mm)
Depth	1.63 in (41.5 mm)

Environment

Ambient Temperature Range - Operational	-40...131 °F (-40...55 °C)
Product Certifications	UL Listed UL Recognized CSA CE

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	21143-8501 R
Discount Schedule	CP2
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------