

# 8501RSD4P14V50

Relay - miniature plug-in - 3A - 4 poles - 6VDC  
coil - pilot light



Price\* : 36.80 USD

8501RSD4P14V50 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

## Main

Product range	8501R
Product type	Miniature Relay
Relay type	Low voltage

## Complementary

Mounting type	Socket
Contact composition	4PDT
[Uc] control circuit voltage	6 V DC
Pilot light	LED green indicator when relay energised
Manual operator	Without test button
Horsepower rating	0.1 at 120 V AC 0.1 at 240 V AC
Breaking capacity	3 A at 120 V AC - resistive control circuit per UL 508 3 A at 277 V AC - resistive control circuit per UL 508 3 A at 30 V DC - resistive control circuit per UL 508 1.5 A at 120 V AC - inductive control circuit per UL 508 0.75 A at 240 V AC - inductive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Gold flashed fine silver
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR45
Height	27.9 mm
Width	0.83 in (21 mm)
Depth	1.63 in (41.5 mm)

## Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	CE CSA UL listed UL recognized

## Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
Nbr. of units in pkg.	25
Package weight(Lbs)	8.999999999999997E-2
Returnability	N
Country of origin	CN

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------