

Product data sheet

Specifications

SQUARE D



NEMA Control Relay, Type X, mechanical latch attachment, 12VDC Coil

8501XDLV51

! Discontinued on: Oct 11, 2019

! Discontinued

Main

Range Of Product	8501X
Relay Type	Control relay
Product Or Component Type	Latching device

Complementary

[Uc] Control Circuit Voltage	12 V DC
Coil Voltage Limits	Operational 0.8...1.1 Uc DC
Inrush Power In Watts	18 W
Sealed Power In Watts	18 W
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	Control circuit 9.03...12.04 lbf.in (1.02...1.36 N.m) screw terminals

Environment

Product Certifications	CSA LR60905 class 3211 02 CE UL recognized E78403 CCN NKCR2
------------------------	---

Ordering and shipping details

Category	21159-8501 X ACCESSORIES
Discount Schedule	CP2
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.