

Product data sheet

Specifications



RELAY 600VAC 10AMP NEMA +OPTIONS

8501XDO20XDLV51

Discontinued on: Oct 11, 2019

Discontinued

Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	2 NO 2 standard contact cartridges
Number Of Poles	2P
Coil Voltage	12 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	UL Listed CSA CE
Operating Time	37 ms - pick-up 45 ms - drop-out
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	7.76 in (197.10 mm)

Ordering and shipping details

Category	21157-8501 XDO (DC)
Discount Schedule	CP2
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.