



Price* : 582.00 USD



8501XDO60XDLV66 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	6 NO 6 standard contact cartridges
Number of Poles	6P
Coil Voltage	230/250 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40...160 °F
Electrical Connection	Screw clamp terminals
Certifications	CSA CE UL listed
Operating Time	37 ms pick-up 45 ms drop-out

Ordering and shipping details

Category	21157 - 8501 XDO (DC)
Discount Schedule	CP2
GTIN	00785901786320
Nbr. of units in pkg.	1
Package weight(Lbs)	3.73
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant
------------------------	-------------------

Will be compliant

REACH

Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
