

8501XLV07

NEMA Control Relay Mechanical Latch Attachment - 550VAC-50Hz/600VAC-60Hz Coil



Price* : 169.00 USD



8501XLV07 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	8501X
Relay type	Control relay
Product or component type	Latching device

Complementary

[Uc] control circuit voltage	600 V AC 60 Hz 550 V AC 50 Hz
Coil Voltage Limits	0.85...1.1 Uc operational AC 50/60 Hz
Coil Inrush Power	148 VA at: 60 Hz 143 VA at: 50 Hz
Coil Sealed Power	23 VA at: 60 Hz 25 VA at: 50 Hz
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	1.02...1.36 N.m control circuit screw terminals

Environment

Product certifications	UL recognized E78403 CCN NKCR2 CSA LR60905 class 3211 02 CE
------------------------	---

Ordering and shipping details

Category	21159 - 8501 X ACCESSORIES
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4000000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
