

# Product data sheet

Specifications

SQUARE D



## NEMA Control Relay, Type X, mechanical latch attachment, 12 VAC 60 Hz coil

8501XLV11

Discontinued on: Oct 11, 2019

Discontinued

### Main

Range Of Product	8501X
Relay Type	Control relay
Product Or Component Type	Latching device

### Complementary

[Uc] Control Circuit Voltage	12 V AC 60 Hz
Coil Voltage Limits	Operational 0.85...1.1 Uc AC 60 Hz
Coil Inrush Power	148 VA 60 Hz
Coil Sealed Power	23 VA 60 Hz
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	Control circuit 9.03...12.04 lbf.in (1.02...1.36 N.m) screw terminals

### Environment

Product Certifications	CSA LR60905 class 3211 02 UL recognized E78403 CCN NKCR2 CE
------------------------	---

### Ordering and shipping details

Category	21159-8501 X ACCESSORIES
Discount Schedule	CP2
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.