



Price* : 336.00 USD



8501XMO40V03Y414 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

| | |
|-----------------------|----------------------------------|
| Range | 8501X |
| Relay Type | Master |
| Product | Relay |
| Current Rating | 20 A AC |
| Contact Configuration | 4 NO 4 master contact cartridges |
| Number of Poles | 4P |
| Coil Voltage | 220 V AC 50 Hz 240 V AC 60 Hz |
| Voltage Rating | 600 V AC |
| Mounting Type | Panel |
| Operating Temperature | -40...160 °F |
| Electrical Connection | Ring tongue |
| Certifications | CSA UL listed CE |
| Operating Time | 15 ms pick-up 16 ms drop-out |

Ordering and shipping details

| | |
|-----------------------|----------------------|
| Category | 21158 - 8501 XO (AC) |
| Discount Schedule | CP2 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant Will be compliant |
|------------------------|--|

| | |
|-------|--|
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
|-------|--|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
