



Price* : 336.00 USD



ⓘ Discontinued

8501XMO40V42 has not been replaced. Please contact your customer care center for more information.

Main

Range	8501X
Relay Type	Master
Product	Relay
Current Rating	20 A AC
Contact Configuration	4 NO 4 master contact cartridges
Number of Poles	4P
Coil Voltage	347 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F
Electrical Connection	Screw clamp terminals
Certifications	UL listed CE CSA
Operating Time	15 ms pick-up 16 ms drop-out

Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	2
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
