

# Product data sheet

Specifications

SQUARE D



## RELAY 600VAC 10AMP NEMA +OPTIONS

8501XO20XLV06

Discontinued on: Oct 11, 2019

Discontinued

### Main

|                       |                                     |
|-----------------------|-------------------------------------|
| Range                 | 8501X                               |
| Relay Type            | Latching                            |
| Product               | Relay                               |
| Current Rating        | 10 A AC<br>5 A DC                   |
| Contact Configuration | 2 NO 2 standard contact cartridges  |
| Number Of Poles       | 2P                                  |
| Coil Voltage          | 440 V AC 50 Hz<br>480 V AC 60 Hz    |
| Voltage Rating        | 600 V AC                            |
| Mounting Type         | Panel                               |
| Operating Temperature | -40...160 °F (-40...71 °C)          |
| Electrical Connection | Screw clamp terminals               |
| Certifications        | CSA<br>UL Listed<br>CE              |
| Operating Time        | 15 ms - pick-up<br>13 ms - drop-out |
| Height                | 3.50 in (88.90 mm)                  |
| Width                 | 2.23 in (56.64 mm)                  |
| Depth                 | 6.54 in (166.12 mm)                 |

### Ordering and shipping details

|                   |                    |
|-------------------|--------------------|
| Category          | 21158-8501 XO (AC) |
| Discount Schedule | CP2                |
| Gtin              | 00785901124320     |
| Returnability     | No                 |
| Country Of Origin | MX                 |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.