

Product data sheet

Specifications

SQUARE D



RELAY 600VAC 10AMP NEMA +OPTIONS

8501XO30XLV07

Discontinued on: Oct 11, 2019

Discontinued

Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	3 NO 3 standard contact cartridges
Number Of Poles	3P
Coil Voltage	550 V AC 50 Hz 600 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	CSA CE UL Listed
Operating Time	15 ms - pick-up 13 ms - drop-out
Height	3.50 in (88.90 mm)
Width	2.23 in (56.64 mm)
Depth	6.54 in (166.12 mm)

Ordering and shipping details

Category	21158-8501 XO (AC)
Discount Schedule	CP2
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.