



Price\* : 360.00 USD



8501XO40XLV12 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	4 NO 4 standard contact cartridges
Number of Poles	4P
Coil Voltage	24 V AC 50 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F
Electrical Connection	Screw clamp terminals
Certifications	UL listed CE CSA
Operating Time	15 ms pick-up 13 ms drop-out

### Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	2.8000000000000003
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---