



Price* : 481.00 USD



8501XO44XLV07 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	4 NO + 4 NC 8 standard contact cartridges
Number of Poles	8P
Coil Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F
Electrical Connection	Screw clamp terminals
Certifications	CSA UL listed CE
Operating Time	15 ms pick-up 13 ms drop-out

Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	3.1000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant
------------------------	-------------------

Will be compliant

REACH

Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
