





NEMA Control Relay, utility relay, 8 NO and 0 NC, 125 VDC coil, pan head screws

8501XUDO80V63Y414

! Discontinued on: Oct 11, 2019

! Discontinued

Main

Range	8501X	
Relay Type	Utility	
Product	Relay	
Current Rating	10 A AC 5 A DC	
Contact Configuration	8 NO 8 standard contact cartridges	
Number Of Poles	8P	
Coil Voltage	125 V DC	
Voltage Rating	250 V DC	
Mounting Type	Panel	
Operating Temperature	-40160 °F (-4071 °C)	
Electrical Connection	Ring tongue	
Certifications	CE UL Listed CSA	
Operating Time	37 ms - pick-up 21 ms - drop-out	
Height	3.56 in (90.42 mm)	
Width	2.23 in (56.64 mm)	
Depth	6.37 in (161.80 mm)	

Ordering and shipping details

Category	21157-8501 XDO (DC)
Discount Schedule	CP2
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov