

8502SAG11V03

Non-Reversing Contactor Size 00, 2-Pole, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 318.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	9 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	00
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

Ordering and shipping details

Category 21191 - 8502,36 SA,SB(NOT S*R,T,W)

Discount Schedule	CP1
GTIN	00785901312581
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------