

# 8502SAG12V06A3

## Non-Reversing Contactor, Size 00, 3-Pole, NEMA 1 +Options



Price\* : 567.00 USD



8502SAG12V06A3 has not been replaced. Please contact your customer care center for more information.

### Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Contactator Type	Non-reversing
Line Rated Current	9 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (ON-OFF)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA
NEMA size	00

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	5
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

**Contractual warranty**

Warranty period	18 months
-----------------	-----------