


8502SAG12V81FF4T

Non-Reversing Contactor, Size 00, 3-Pole, NEMA 1 +Options



Price* : 1,058.00 USD



8502SAG12V81FF4T has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------------------------|--|
| Product or component type | Contacteur |
| Type | 8502S |
| Control Circuit Type | Control circuit transformer |
| Control Circuit Voltage | 480 V (primary), 120 V (secondary) |
| Contactor Type | Non-reversing |
| Line Rated Current | 9 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 2 fuses (primary), 1 fuse (secondary) |
| Electrical connection | Screw clamp terminals |
| Enclosure Type | NEMA 1 painted sheet steel |
| Product certifications | CSA UL listed |
| NEMA size | 00 |
| Height | 15.87 in (403 mm) |
| Depth | 5 in (127 mm) |
| Width | 6.34 in (161 mm) |

Ordering and shipping details

| | |
|----------|------------------------------------|
| Category | 21191 - 8502,36 SA,SB(NOT S*R,T,W) |
|----------|------------------------------------|

| | |
|-----------------------|--------------------|
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 5.8200000000000003 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant on 3Q2014 Will be compliant on 3Q2014 |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|