

8502SAO12V08

Non-Reversing Contactor, Size 00, 3-Pole, Open Style

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 329.00 USD



Main

Product or component type	Contactors
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	208 V AC 60 Hz
Contactors Type	Non-reversing
Line Rated Current	9 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	Not rated (open device)
Product certifications	CSA UL listed
NEMA size	00
Height	4.33 in (110 mm)
Depth	4.21 in (107 mm)
Width	3.23 in (82 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901340683
Nbr. of units in pkg.	1
Package weight(Lbs)	4
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------