


8502SBA5V02A

Non-Reversing Contactor, Size 0, 1-Pole, NEMA 12 +Options



Price* : 867.00 USD



8502SBA5V02A has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactator Type	Non-reversing
Line Rated Current	18 A
Number of Poles	1P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 12 painted sheet steel
Product certifications	UL listed CSA
NEMA size	0
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	16.859999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------