

# 8502SBG1V01C

## Non-Reversing Contactor, Size 0, 2-Pole, NEMA 1 +Options



Price\* : 611.00 USD



8502SBG1V01C has not been replaced. Please contact your customer care center for more information.

### Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	24 V AC 60 Hz
Contactator Type	Non-reversing
Line Rated Current	18 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	0

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

Offer Sustainability

---

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---