

8502SBG2V02CSX10

Non-Reversing Contactor, Size 0, 3-Pole, NEMA 1 +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 939.50 USD



Main


Product or component type	Contacteur
Type	8502S
Control Circuit Type	Separate control circuit
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	1 NO
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	0
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------