

# 8502SBG2V08

## Non-Reversing Contactor, Size 0, 3-Pole, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 446.00 USD



### Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	208 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	0
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901761211
Nbr. of units in pkg.	1
Package weight(Lbs)	6.419999999999999
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------