

# 8502SBG2V81C6F4T

## Non-Reversing Contactor, Size 0, 3-Pole, NEMA 1 +Options



Price\* : 1,350.00 USD



8502SBG2V81C6F4T has not been replaced. Please contact your customer care center for more information.

### Main

|                           |  |
|---------------------------|--|
| Product or component type | Contactor  |
| Type                      | 8502S  |
| Control Circuit Type      | Control circuit transformer                                      |
| Control Circuit Voltage   | 480 V (primary), 120 V (secondary)                               |
| Contactor Type            | Non-reversing  |
| Line Rated Current        | 18 A   |
| Number of Poles           | 3P   |
| Phase                     | 3 phases   |
| Horsepower Rating         | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC |
| System Voltage            | 600 V AC   |
| Control Units             | Selector switch (ON-OFF)   |
| Pilot Light               | No indicator   |
| Auxiliary Contacts        | Without  |
| Control Circuit Fusing    | 2 fuses (primary)  |
| Electrical connection     | Screw clamp terminals  |
| Enclosure Type            | NEMA 1 painted sheet steel                                       |
| Product certifications    | CSA<br>UL listed   |
| NEMA size                 | 0  |
| Height                    | 15.87 in (403 mm)  |
| Depth                     | 5 in (127 mm)  |
| Width                     | 6.34 in (161 mm)   |

### Ordering and shipping details

|          |                                    |
|----------|------------------------------------|
| Category | 21191 - 8502,36 SA,SB(NOT S*R,T,W) |
|----------|------------------------------------|

|                       |                    |
|-----------------------|--------------------|
| Discount Schedule     | CP1                |
| Nbr. of units in pkg. | 1                  |
| Package weight(Lbs)   | 28.350000000000001 |
| Returnability         | N                  |
| Country of origin     | MX                 |

**Offer Sustainability**

|                        |  |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant on 3Q2014<br>Will be compliant on 3Q2014   |
| REACH                  | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|