

Product data sheet

Specifications



NEMA Contactor, Type S, nonreversing, Size 0, 18A, 2 HP at 230 VAC, 1 phase, up to 100 kA, 1 pole, 120 VAC coil, NEMA 1

8502SBG5V02

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	1P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Sccr	Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	10.00 in (254 mm)
Width	5.98 in (152 mm)
Depth	5.28 in (134 mm)

Environmental

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL listed file E78351 CCN NLDX CSA
----------------	---------------------------------------

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Gtin	785901018582
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	5.28 in (13.4 cm)
Package 1 Weight	5.00 lb(US) (2.268 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov