

Product data sheet

Characteristics

8502SBT45V02

Non-Reversing Contactor, Size 0, 3-Pole, NEMA 7/9

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,979.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	18 A
Number of Poles	1P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 7/9 cast aluminium type: bolted
Product certifications	CSA UL listed
NEMA size	0
Height	438 mm
Depth	10.98 in (279 mm)
Width	14.25 in (362 mm)

Ordering and shipping details

Category 21202 - 8502,36 S*R,S*T,S*W

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------