

Product data sheet

Characteristics

8502SBW15V02

Non-Reversing Contactor, Size 0, 1-Pole, NEMA 4/4X

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 860.00 USD



Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactator Type	Non-reversing
Line Rated Current	18 A
Number of Poles	1P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA UL listed
NEMA size	0
Height	13.19 in (335 mm)
Depth	7.13 in (181 mm)
Width	6.38 in (162 mm)

Ordering and shipping details

Category 21203 - 8502,36 W/STAINLESS ENCLOSURES

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	35.300000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------